

HPLC Manifold With Stainless Steel Fittings for Round Style or Quick-Disconnect Safety Disposal Can - 28168

Product Images





Short Description

- Collect waste from up to four waste lines into a single intake fitting
- Complies with OSHA and NFPA Code 30
- For use on round containers

Description

Safely collect waste from up to four waste lines from HPLC processes into a single intake fitting. Kit accommodates either 1/16" (2-mm) OD or 1/8" (3-mm) OD lines. Approximately 3-1/2" (89-mm) long and made of No. 316 gauge stainless steel, manifold fits only a stainless steel intake fitting. Four ports are tapped to accommodate 1/4-28 threads of the supplied fittings. PEEK™ fittings include four each: 1/16" (2-mm) and 1/8" (3-mm) OD tube fittings with corresponding PCTFE ferrules for compression fit of waste line. Four plug caps are provided to close unused ports. Multiple manifolds may be used on a custom-designed quick-disconnect container as long as one fitting remains unused. Safety container with manifold installed is OSHA compliant and meets NFPA Code 30. Use on round containers; not for use on oval style can.

Specifications

Model No	28168
UPC	697841097216
Brand	Justrite
International Model No.	28168
FM Approval	Yes
Color	Silver
Material Specifications	Stainless Steel
Dimensions, Exterior	2.125" H x 2.75" W x 8.75" L
Dimensions, Exterior	54mm H x 70mm W x 222mm D x 222mm L
Net Weight, lbs	0.6
Net Weight, kg	0.3